

# ACCU-CAL™ 50V Visible Radiometer

CE Marked – Available Globally

Consistent curing requires periodic monitoring of visible energy intensity or dose. The ACCU-CAL™ 50V radiometer is simple to operate and offers repeatable measurement of visible light. The ACCU-CAL 50V can measure visible light energy emitted from lightguides (3 mm, 5 mm, and 8 mm), flood systems, and conveyors. With a spectral sensitivity from 395 to 465 nm (blue portion of the visible spectrum), the ACCU-CAL 50V measures intensities from 1 mW/cm<sup>2</sup> to 40 W/cm<sup>2</sup>. A specially designed photo sensor assembly protects the photo sensor from the high temperatures sometimes associated with today's high-intensity spot lamps.

**Simple to Operate • Set Screw Locks Lightguide in Place • PTB and NIST Traceable**



ACCU-CAL 50V for measuring floods and conveyors only - PN 40044



ACCU-CAL 50V for measuring spots, floods, and conveyors

## THREE REASONS TO USE A VISIBLE RADIOMETER

- **Maintaining a Light Curing Process** – A radiometer measures whether a light curing system is providing intensity above the “bulb change” intensity. Radiometers provide the same monitoring control for light curing processes that thermometers provide for thermal processes.
- **Providing a Worker Friendly Light Curing Process** – The ACCU-CAL 50V is sufficiently sensitive to measure the intensity of stray or reflected visible light (as little as 1 mW/cm<sup>2</sup>).
- **Measuring Transmission Rates through Substrates** – A radiometer can be used to measure the transmission rates of various wavelengths through substrates that absorb UV and/or visible light. To assure an effective curing process, it is critical to measure the light intensity reaching the resin below the intervening substrate.

## SPECIFICATIONS

<b>Spectral Sensitivity</b>	395 to 465 nm
<b>Intensity Range</b>	1 mW/cm <sup>2</sup> to 40 W/cm <sup>2</sup>
<b>Resolution</b>	Intensity (1 mW/cm <sup>2</sup> ; to three significant digits) Dose (1 mJ/cm <sup>2</sup> )
<b>Calibration Period</b>	12 months
<b>Operating Temperature Ranges</b>	Optometer: +5 to +40°C Detector: 120°C continuous, Peak 200°C
<b>Measurement Modes</b>	Intensity (mW/cm <sup>2</sup> and W/cm <sup>2</sup> ) Peak Intensity (mW/cm <sup>2</sup> and W/cm <sup>2</sup> ) Dose (J/cm <sup>2</sup> )
<b>Light Sources</b>	Lightguides (3 mm, 5 mm, and 8 mm) Floods/Conveyors
<b>Power Supply</b>	Two (2) AA batteries
<b>Battery Life</b>	250 hours (automatic shutoff after 1 hour)
<b>Sensor Dimensions</b>	Photo Sensor Diameter = 9 mm Diameter = 37 mm Thickness = 8 mm Cable Length = 1 M
<b>Meter Dimensions</b>	120 mm (Length) x 65 mm (Width) x 23 mm (Thickness)

## RADIOMETERS and ACCESSORIES

Product	Part Number	Description
ACCU-CAL™ 50V for Flood Lamps and Conveyors	<b>40044</b>	Complete radiometer (without lightguide adapters or lightguide simulator*); includes storage/carrying case
ACCU-CAL 50V for Spot and Flood Lamps and Conveyors	<b>40043</b>	Complete radiometer with lightguide adapters (3 mm, 5 mm, and 8 mm); includes storage/carrying case
Flood to Spot Adapter Kit	<b>39554</b>	Kit includes three lightguide adapters (3 mm, 5 mm, and 8 mm) and a lightguide simulator*
3 mm Lightguide Adapter	<b>39556</b>	Fits 3 mm ID lightguides (5 mmOD)
5 mm Lightguide Adapter	<b>39557</b>	Fits 5 mm ID lightguides (7 mm OD)
8 mm Lightguide Adapter	<b>39558</b>	Fits 8 mm ID lightguides (10 mm OD)
5 mm Lightguide Simulator	<b>38408</b>	5 mm lightguide simulator with a standard D connection

\*A lightguide simulator is used to measure direct spot lamp intensity (required to calculate lightguide transmission)

© 2008-2010 DYMAX Corporation. All rights reserved. All trademarks in this guide, except where noted, are the property of, or used under license by DYMAX Corporation, U.S.A. The data contained in this bulletin is of a general nature and is based on laboratory test conditions. DYMAX Europe GmbH does not warrant the data contained in this bulletin. Any warranty applicable to products, its application and use is strictly limited to that contained in DYMAX Europe GmbH's General Terms and Conditions of Sale published on our homepage [http://www.dymax.com/de/pdf/dymax\\_europe\\_general\\_terms\\_and\\_conditions\\_of\\_sale.pdf](http://www.dymax.com/de/pdf/dymax_europe_general_terms_and_conditions_of_sale.pdf). DYMAX Europe GmbH does not assume any responsibility for test or performance results obtained by users. It is the user's responsibility to determine the suitability for the product application and purposes and the suitability for use in the user's intended manufacturing apparatus and methods. The user should adopt such precautions and use guidelines as may be reasonably advisable or necessary for the protection of property and persons. Nothing in this bulletin shall act as a representation that the product use or application will not infringe a patent owned by someone other than DYMAX Corporation or act as a grant of license under any DYMAX Corporation Patent. DYMAX Europe GmbH recommends that each user adequately test its proposed use and application of the products before actual repetitive use, using the data contained in this bulletin as a general guide. LIT236EU 8/15/2008

DYMAX Corporation  
860.482.1010  
info@dymax.com  
[www.dymax.com](http://www.dymax.com)

DYMAX Europe GmbH  
+49 (0) 611.962.7900  
info\_de@dymax.com  
[www.dymax.de](http://www.dymax.de)

DYMAX UV Adhesives &  
Equipment (Shenzhen) Co Ltd  
+86.755.83485759  
dymaxasia@dymax.com  
[www.dymax.com.cn](http://www.dymax.com.cn)

DYMAX Asia (Hong Kong) Ltd  
+852.2460.7038  
dymaxasia@dymax.com  
[www.dymax.com.cn](http://www.dymax.com.cn)

DYMAX Korea LLC  
82.2.784.3434  
info@dymax.kr  
[www.dymax.co.kr](http://www.dymax.co.kr)

