

Video: vacuum mixing, degassing, and set-up of THINKY ARV-501 Mixer

Our partners at THINKY, makers of planetary centrifugal mixers, have produced a video detailing how to use the [THINKY ARV-501 vacuum mixer](#), with or without the vacuum mixing functionality. In this video, you can see how the user interface works, how to set up a program, and learn about the mixer's PC interface:

The THINKY ARV-501 allows contactless mixing and degassing of up to 700g of materials, be they adhesives, gels, inks, pastes, powders or other engineering compounds. It is a part of our complete [THINKY mixer range](#). With no clean-up required between batches and consistent, homogeneous mixing results, you can save time and effort on mixing and have confidence in a reliable process. [Let us know](#) if you'd like to explore THINKY mixers further.

Supplied by:

intertronics

INTERTRONICS

12a Station Field Industrial Estate, Banbury Road, Kidlington

Oxfordshire England OX5 1JD

t 01865 842842 e info@intertronics.co.uk

Last updated: May 2021

Statements, technical information and recommendations contained herein are based on tests we believe to be reliable but they are not to be construed in any manner as warranties expressed or implied. The user shall determine the suitability of the product for his intended use and the user assumes all risk and liability whatsoever in connection therewith.