

Flow-Seal Pens and Bottles



Description

Flow-Seal dispensing pens and bottles are designed to apply controlled amounts of flux, solvents, inks, cleaners, coatings, lubricants, stains, paints & other fluids. The Flow-Seal cap, with its integral valve, provides superior control and prevents flooding and spattering. The Flow-Seal cap allows for easy removal of a choice of tips when cleaning or replacing, and creates a secondary mini reservoir to hold the fluid. Standard reservoir and open top bottles allow fluids to evaporate in the working area. With Flow-Seal this is prevented, thereby saving cost, delivering the product where it is needed and helping to improve working conditions. Flow-Seal Pens & Bottles are designed to contain and dispense fluids of a wide range of viscosity and pigmentation.

Flow-Seal Pens and Bottles



Flow-Seal Dispensing Pens

Flow-Seal Pens are available with plastic reservoirs or ESD safe metal reservoirs. The pen is in two parts (cap and reservoir) and is easily assembled. The reservoir should be filled with material to within 19mm of the top; this air chamber allows for the valve cap to be pressed securely in position. Priming is achieved by depressing the nib while the pen is vertical. The nibs are interchangeable.

Flow-Seal Pens and Bottles



Flow-Seal Dispensing Bottles

Flow-Seal Bottles are available in 2oz and 4oz sizes, with interchangeable nib types to suit the material and application. The caps screw on, which allows convenient refilling.

Features & Benefits

- Fluid control

Flow-Seal Pens and Bottles



- Similar to a felt-tip pen
- Prevents unwanted evaporation
- Controls worker exposure to potentially hazardous vapours & fumes
- ESD safe
- Clean
- Convenient

Ordering Information

Part number	Description	Quantity
Pens and Bottles		
IJF FV-0100	Flow-Seal Pen	1
IJF FV-0200	Flow-Seal Pen ESD Safe	1
IJF FV-0300	Flow-Seal Bottle 2oz	1
IJF FV-0400	Flow-Seal Bottle 2oz Aluminium	1
IJF FV-0500	Flow-Seal Bottle 4oz	1

Flow-Seal Pens and Bottles



Part number	Description	Quantity
FIS FV-0600-EU-NN	Flow-Seal Jumbo Pen	1
All are supplied with the IJF 381-8425-AC nib except the “Jumbo” Pen		
Replacement Nibs		
IJF 381-8425-AC	Nib – Acrylic Chisel	10
IJF 381-8425-AB	Nib – Acrylic Bullet	10
IJF 381-8425-AP	Nib – Acrylic Point	10
IJF 381-8425-PC	Nib – Polyester Chisel	10
IJFFV-381-600-PB	Nib – Polyester Blunt	10

Let’s start by talking about your application

Flow-Seal Pens and Bottles



01865



orders@intertronics.co.uk

842842

- Name*
- Company*
- Phone*
- Email*
- Post code*

If you're in the UK, knowing your postcode would help us get in touch even more quickly. If you're outside the UK, please indicate your country.

-
- Tell us about your application

Flow-Seal Pens and Bottles



Any information that you submit using this form will be processed according to our [privacy policy](#).

■ Name

This field is for validation purposes and should be left unchanged.

Submit

Supplied by:

intertronics

INTERTRONICS

12a Station Field Industrial Estate, Banbury Road, Kidlington

Oxfordshire England OX5 1JD

t 01865 842842 e info@intertronics.co.uk

Last updated: November 2022 Version: 4.3

Statements, technical information and recommendations contained herein are based on tests we believe to be reliable but they are not to be construed in any manner as warranties expressed or implied. The user shall determine the suitability of the product for his intended use and the user assumes all risk and liability whatsoever in connection therewith.